



BURNDY Catalog Number
UPC Number

YAV25L3
7818100256599

Description

1/0 HVYDTY RING 1/2 STUD,2.089
IN L

Status

Active

Web Use

BURNDY Product Line

Dimensional

Tongue Angle	Straight
Strip Length	11/16
Length (in)	2.09
Tongue Type	Ring
Pad Width (in)	0.88

General

Product Description

Copper Compression Lug, Heavy Duty, Ring Tongue, 1 Hole w/ Inspection Hole, AN-1/0 Flex, 1/2" Stud, Short Barrel, Electro-Tin Plated

Conductor(s)

Aircraft Cable Size (Range)	AN 0
Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	1/0 AWG

Physical

Type of Plating	Tin - Electro Plated
Connector Type	Terminal
Plated (Yes or No)	Y

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
Mil-Spec Class Code	Class 1
CULUS	N
Industry Standards	UL467, Military Specified (Mil-Spec)

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175