



BURNDY Catalog Number
UPC Number
Description
Status

YDS28AT
7818108210911
4/0 AL FULL TEN SPLICE
Active

Web Use
BURNDY Product Line

B Length (Fraction)
Length (in)
B Length (in)
Length (Fraction)

Dimensional
5-9/53
10.47
5.17
10-1/2

Product Description

General
Aluminium Hysplice, 10-1/2 in L,
Full Tension Sleeve for All
Aluminum Compressed and
Compact Conductors

Prefilled (Oxide Inhibitor)

Y

ACSR Size (Range)
ACSR Compact Size (Range)
AAAC 6201 Size (Range)
Aluminum Size (Range)
AAAC 5005-Size (Range)

Conductor(s)
N/A
4/0 AWG
N/A
4/0 AWG
N/A

Type of Plating
Plated (Yes or No)
Index Number
Product Material

Physical
Unplated
N
249
Aluminum

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Approvals / Certifications
N
N
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175