



BURNDY Catalog Number
UPC Number
Description
Status

YGHC34C34
 7818102210822
 300-500 TO 300-500 GRD C
 Active

Web Use
 BURNDY Product Line

B Length (in)
 Diameter (in) - Total

Dimensional

1.10
 2.91

General

Copper Compression C Connector,
 300-500 kcmil (Run & Tap)

Product Description

Conductor(s)

Copper Tap Range
 Copper Stranded Run (Range)
 Rod Size Run (Range)
 Copper Solid Tap (Range)
 Rebar Run Size (Range)
 Copper Solid Run Size (Range)

300-500
 300-500
 3/8
 N/A
 N/A
 N/A

Physical

Type of Plating
 Connector Type
 Plated (Yes or No)
 Index Number
 Product Material

Unplated
 Tap
 N
 1011
 Copper

Approvals / Certifications

Rated for Direct Burial
 UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Y
 Y
 Y
 Compliant
 N
 N
 UL468A-468B,UL467,IEEE 837

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175