

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301050035](#)  
**Status:** **Active**  
**Overview:** Specialty Lighting  
**Description:** Watertite® Wet Location 35W 12V Flood Light with In-line Transformer, Screw Release Guard, 14/2 SOOW, Overall Length 7.62m (50.0')

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR85374

**General**

Product Family      Portable Lighting  
 Series      [130105](#)  
 NEMA Configuration      NEMA 5-15  
 NEMA Rating      NEMA 4X  
 Outlet      None  
 Overview      [Specialty Lighting](#)  
 Product Literature Order No      987650-8052  
 Product Name      Watertite®  
 Type      Hand Lamps, Specialty Light  
 UPC      78678861532  
 Woodhead      Yes

**Physical**

Cord Length - Primary      3.04m (10.0')  
 Cord Length - Secondary      15.24m (50.0')  
 Depth      N/A  
 Duty      Wet Location  
 Guard Included      No  
 Guard Type      N/A  
 Height      127.00mm (5.000")  
 Length      228.60mm (9.000")  
 Material - Guard      #10 Gauge Vinyl Coated Steel  
 Mounting Style      Hand Held  
 Packaging Type      Carton  
 Socket Construction      N/A

**Electrical**

Bulb Type      Quartz Halogen  
 Cord Type - Primary      16/3 SOOW  
 Cord Type - Secondary      14/2 SOOW  
 Lamp Type      PAR36  
 Lamp Wattage - Maximum      35W  
 Lumens      350  
 On/Off Switch      No  
 Voltage (Fixture) - Maximum      120VAC 60 HZ

**Material Info**

Old Part Number      1612



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

**Search Parts in this Series**

[130105](#) Series