



## ID SW REDUCER



Size	Symbol	Symbol No.	inches				millimeters			
			ØB1	ØB2	D	L	ØB1	ØB2	D	L
2	53	40-2029	2.140	1.900	0.070	18	54.4	48.3	1.8	457.2
2½	63	40-2529	2.640	2.140	0.070	18	67.1	54.4	1.8	457.2
3	78	40-3029	3.140	2.640	0.070	18	79.8	67.1	1.8	457.2
3½	91	40-3529	3.640	3.140	0.070	18	92.5	79.8	1.8	457.2
4	103	40-4029	4.140	3.640	0.070	18	105.2	92.5	1.8	457.2
4½	116	40-4529	4.690	4.140	0.095	18	119.1	105.2	2.4	457.2
5	129	40-5029	5.190	4.690	0.095	18	131.8	119.1	2.4	457.2
6	155	40-6029	6.190	5.190	0.095	18	157.2	131.8	2.4	457.2

## ID SW MULTIFIT ADAPTER



Size	Symbol	Symbol No.	inches					millimeters				
			ØC	D	ØG	ØH	L	ØC	D	ØG	ØH	L
2	53	40-2037	2.170	0.070	2.424	2.239	13	55.1	1.8	61.6	56.9	330.2
2½	63	40-2537	2.670	0.070	2.924	2.739	13	67.8	1.8	74.3	69.6	330.2
3	78	40-3037	3.170	0.070	3.549	3.239	13	80.5	1.8	90.1	82.3	330.2
3½	91	40-3537	3.670	0.070	4.061	3.709	13	93.2	1.8	103.1	94.2	330.2
4	103	40-4037	4.170	0.070	4.620	4.109	13	105.9	1.8	117.3	104.4	330.2
4½	116	40-4537	4.730	0.095	4.831	4.750	13	120.1	2.4	122.7	120.7	330.2
5	129	40-5037	5.230	0.095	5.650	5.289	13	132.8	2.4	143.5	134.3	330.2
6	155	40-6037	6.230	0.095	6.686	6.259	13	158.2	2.4	169.8	159.0	330.2