

Safety Switches Heavy Duty, Type TH

Spec-Setter™ Safety Switches

30-1200 Amperes

240 Volts AC

250 Volts DC

Section 2

Fusible, Two-pole, 240 Volts AC; 250 Volts DC

Ampere Rating	Enclosure Type	HP, 240 Vac, NEC Std, 1-ph	HP, 240 Vac, NEC Std, 3-ph	HP, 240 Vac, Time Delay, 1-ph	HP, 240 Vac, Time Delay, 3-ph	HP, 125 Vdc	HP, 250 Vdc	Product Number	List Price GO-131
30A	NEMA Type 1	1 1/2	3	3	7 1/2	-	5	TH3221	\$153.00
60A	NEMA Type 1	3	7 1/2	10	15	5	10	TH3222	\$300.00
100A	NEMA Type 1	7 1/2	15	15	30	-	20	TH3223	\$467.00
200A	NEMA Type 1	15	25	-	60	-	40	TH3224	\$830.00
400A	NEMA Type 1	-	50	-	125	-	50	TH3225	\$1948.00
600A	NEMA Type 1	-	75	-	200	-	-	TH3226	\$3670.00
800A	NEMA Type 1	-	-	-	-	-	-	TC72267 ^{1,3}	\$6996.00
1200A	NEMA Type 1	-	-	-	-	-	-	TC72268 ¹	\$9614.00
30A	NEMA Type 3R	1 1/2	3	3	7 1/2	-	5	TH3221R	\$291.00
60A	NEMA Type 3R	3	7 1/2	10	15	5	10	TH3222R	\$542.00
100A	NEMA Type 3R	7 1/2	15	15	30	-	20	TH3223R	\$702.00
200A	NEMA Type 3R	15	25	-	60	-	40	TH3224R	\$1006.00
400A	NEMA Type 3R	-	50	-	125	-	50	TH3225R	\$2450.00
600A	NEMA Type 3R	-	75	-	200	-	50	TH3226R	\$4590.00
800A	NEMA Type 3R	-	-	-	-	-	-	TC72267R ^{2,3}	\$8975.00
1200A	NEMA Type 3R	-	-	-	-	-	-	TC72268R ²	\$13127.00
30A	NEMA Type 4/4X	1 1/2	3	3	7 1/2	-	5	TH2221SS	\$1218.00
60A	NEMA Type 4/4X	3	7 1/2	10	15	5	10	TH2222SS	\$1463.00
100A	NEMA Type 4/4X	7 1/2	15	15	30	-	20	TH3223SS	\$3309.00
200A	NEMA Type 4/4X	15	25	-	60	-	40	TH3224SS	\$4538.00
400A	NEMA Type 4/4X	-	50	-	125	-	50	TH3225SS	\$9114.00
600A	NEMA Type 4/4X	-	75	-	200	-	50	TH3226SS	\$13008.00
30A	NEMA Type 5, 12	1 1/2	3	3	7 1/2	-	5	TH2221J	\$295.00
60A	NEMA Type 5, 12	3	7 1/2	10	15	5	10	TH2222J	\$398.00
100A	NEMA Type 5, 12	7 1/2	15	15	30	-	20	TH3223J	\$678.00
200A	NEMA Type 5, 12	15	25	-	60	-	40	TH3224J	\$1058.00
400A	NEMA Type 5, 12	-	50	-	125	-	50	TH3225J	\$2623.00
600A	NEMA Type 5, 12	-	75	-	200	-	50	TH3226J	\$4281.00

Fusible, Three-wire SN, 120/240 and 240 Volts AC

Ampere Rating	Enclosure Type	HP, 240 Vac, NEC Std, 1-ph	HP, 240 Vac, NEC Std, 3-ph	HP, 240 Vac, Time Delay, 1-ph	HP, 240 Vac, Time Delay, 3-ph	HP, 125 Vdc	HP, 250 Vdc	Product Number	List Price GO-131
30A	NEMA Type 1	1 1/2	3	3	7 1/2	-	5	TH3221	\$153.00
60A	NEMA Type 1	3	7 1/2	10	15	5	10	TH3222	\$300.00
100A	NEMA Type 1	7 1/2	15	15	30	-	20	TH3223	\$467.00
200A	NEMA Type 1	15	25	-	60	-	40	TH3224	\$830.00
400A	NEMA Type 1	-	50	-	125	-	50	TH3225	\$1948.00
600A	NEMA Type 1	-	75	-	200	-	50	TH3226	\$3670.00
800A	NEMA Type 1	-	-	-	-	-	-	TC72267 ^{1,3}	\$6996.00
								TNI67	\$490.00
1200A	NEMA Type 1	-	-	-	-	-	-	TC72268 ^{1,3}	\$9614.00
								TNI68A	\$675.00
30A	NEMA Type 3R	1 1/2	3	3	7 1/2	-	5	TH3221R	\$291.00
60A	NEMA Type 3R	3	7 1/2	10	15	5	10	TH3222R	\$542.00
100A	NEMA Type 3R	7 1/2	15	15	30	-	20	TH3223R	\$702.00
200A	NEMA Type 3R	15	25	-	60	-	40	TH3224R	\$1006.00
400A	NEMA Type 3R	-	50	-	125	-	50	TH3225R	\$2450.00
600A	NEMA Type 3R	-	75	-	200	-	50	TH3226R	\$4590.00
800A	NEMA Type 3R	-	-	-	-	-	-	TC72267R ^{2,3}	\$8975.00
								TNI67	\$490.00
1200A	NEMA Type 3R	-	-	-	-	-	-	TC72268R ^{2,3}	\$13127.00
								TNI68A	\$675.00
30A	NEMA Type 4/4X	1 1/2	3	3	7 1/2	-	5	TH3221SS	\$1260.00
60A	NEMA Type 4/4X	3	7 1/2	10	15	5	10	TH3222SS	\$1526.00
100A	NEMA Type 4/4X	7 1/2	15	15	30	-	20	TH3223SS	\$3309.00
200A	NEMA Type 4/4X	15	25	-	60	-	40	TH3224SS	\$4538.00
400A	NEMA Type 4/4X	-	50	-	125	-	50	TH3225SS	\$9114.00
600A	NEMA Type 4/4X	-	75	-	200	-	50	TH3226SS	\$13008.00
30A	NEMA Type 5, 12	1 1/2	3	3	7 1/2	-	5	TH3221J	\$345.00
60A	NEMA Type 5, 12	3	7 1/2	10	15	5	10	TH3222J	\$462.00
100A	NEMA Type 5, 12	7 1/2	15	15	30	-	20	TH3223J	\$678.00
200A	NEMA Type 5, 12	15	25	-	60	-	40	TH3224J	\$1058.00
400A	NEMA Type 5, 12	-	50	-	125	-	50	TH3225J	\$2623.00
600A	NEMA Type 5, 12	-	75	-	200	-	50	TH3226J	\$4281.00

¹Class L fuses are only applicable when used with 800 and 1200A Type TC Safety Switches (e.g. TC72367).

²Not CSA certified.

³Order switch and neutral separately.



Publications and Reference: See Section 22 for a complete list of additional product-related publications