



**Search Parameters:**

[e-Catalog](#) > [Circuit Breakers](#) > Residential Circuit Breakers

**Circuit Breakers, Residential Circuit Breakers**

Product #: THQL32040

Short Description: THQL 3 POLE 240V 10K IC 40 AMP

[Print This Page](#)

[Email This Page](#)

**SPECIFICATIONS**

Category	Feeder Plug-in Circuit Breakers
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	40A
System Voltage	120 Vac , 120/240 Vac , 240 Vac
Poles	3
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Product Line	Q-Line (Plug-In)
UL File #	E11592
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No
GO Schedule	138
UPC	078316401303
List Price	\$165



[View Larger](#)

**Publications/Resources**

[THQL32040](#)

**Additional Resources for Feeder Plug-in Circuit Breakers**

[Application and Technical](#)

[Installation and Instruction](#)

[Time Current Curves](#)

[Buy Log :1-5](#)

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QL breakers are plug-in versions of the Q Line used for connection to load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications.

