



PRODUCT SEARCH

 SUPP
 DIST
[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**TERMINALS**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps &
Miscellaneous](#)**Name:**

Shank Hex Shank Size 5/16" (7.9 mm) Min. Chuck Size 3/8" (9.5 mm) Use With 9/16" - 1-3/16" (14.3 - 30.2 mm) Hole Saws

Cat #:

38524

UPC #:

38524

Spec:**Description:**

The best arbor in the industry ensures a solid connection without any gaps or wobbling. Arbors include replaceable high speed pilot drill. Pilot drills have unique split point tip design. Use with Greenlee bimetal hole saws, recessed light hole saws, and carbide grit hole saws (carbide tipped pilot drill sold separately). Can be used with Greenlee #901, #902 and #904 bit extensions.



© 2007 Greenlee Textron Inc., a subsidiary of **Textron Inc.** All rights reserved.

[Privacy Policy](#) **[Terms of Use](#)** **[Careers](#)**