



PRODUCT SEARCH

[> SUPP](#)
[> DIST](#)
[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**INSTALLATION**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

Piston for 2" Conduit 1

Cat #:

613

UPC #:

16511

Spec:

Capacity 1/2 " - 4" conduit (5" and 6" with optional foam pistons)
 see page 98 Power Source 690: 120 VAC Weight 50 lbs. (22.7 kg)
 Air Flow 120 cfm Pressure Will lift 110" (2794 mm) of water

Description:

Rugged, self-contained unit includes everything you need to blow or vacuum fish line, poly line or measuring tape.

- Durable tank and accessory storage box are corrosion, chemical and impact resistant polyethylene.
- Designed for the jobsite, 10' (3.05 m) long hose, large heavy-duty wheels and removable accessory box.
- Large 11 gallon (41.6 l) tank makes the 690 excellent for vacuuming water and debris.

© 2007 Greenlee Textron Inc., a subsidiary of **Textron Inc.** All rights reserved.

[Privacy Policy](#) [Terms of Use](#) [Careers](#)