



PRODUCT SEARCH

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**PRODUCTS**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

61PTS SHORTY, 62PTS AND 61/62 PTS BIG SHANK SHORTY NAIL EATER II® BITS HOLE DIA. 1in. 25.4mm HEX SHANK 7/16in. 11.1mm

**Cat #:**

62PTS-1

**UPC #:**

31798

**Spec:**

Overall Length 7-5/8" (193.7 mm) Twist Length 5" (127 mm) Electric drill required 61 PTS - 5/8" through 61 PTS - 1", minimum 3/8" drill; All Big Shank, 1/2" drill.

**Description:**

Patented new design for improved cutting and cleaner holes. Self-feeding screw point draws bit through wood. Unique patented design cutting angle - smoother starts, reduced cutting loads. Made of super tough heat treated steel; cuts through nails and provides longer life. "Shorty" bits - for working in tight places, yet still can go through three abutting 2 x 4s. See "Bit Extensions" if more length is required (see page 68). P.O.P. packaged.



© 2007 Greenlee Textron Inc., a subsidiary of [Textron Inc.](#) All rights reserved.

[Privacy Policy](#) [Terms of Use](#) [Careers](#)