



PRODUCT SEARCH

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**INSTALLATION**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

2 Rigid, 2 Swivel Caster Set, 4in. Diameter

Cat #:

696

UPC #:

15341

Spec:

Capacity: 1600 lbs. (726 kg); Ship Weight: 13 lbs. (6 kg); Tread: 2in. (51 mm)

Description:

- Caster bolt patter 2-7/8in. X 3-1/4in.
- Polyolefin-injected molded hard casters: stain-resistant, chemical-resistant, and non-marking.
- Each caster set includes (16) 3/8-16 x 1in. self-threading mounting screws.

© 2007 Greenlee Textron Inc., a subsidiary of [Textron Inc.](#) All rights reserved.[Privacy Policy](#) [Terms of Use](#) [Careers](#)