



GREENLEE.
A Textron Company

MADE FOR THE TRADE!™



DIE 1" CONDUIT

Die, 1" conduit size, SPEED PUNCH™ System

Cat No: 52047820

UPC No: 783310092803

Description

- SPEED PUNCH® saves time and money with every hole.
- Up to 3X's faster setup and disassembly.
- No-Thread punch design eliminates cross-threading.
- Available in 3/4" - 2" conduit sizes and punch kits

Specifications

- Application : For punching conduit sized holes in mild steel, aluminum, fiberglass, and plastic.
- Capacity : Mild steel up through 10 gauge (3.5 mm).
- Diameter : Actual hole size: 1.362" (34.6 MM)
- Draw Studs : Std Draw Stud: 7212SP11 (3/4" x 4.77") Long Draw Stud: 7212SP12 (3/4" x 5.63") for use with 746 Hydraulic Ram
- Driver : Use with Greenlee Hydraulic Drivers - Quick Draw® Flex (7704SB), Quick Draw® Standard (7804SB), Quick Draw® 90 (7904SB) and Hydraulic Ram (746 with 7212SP12 Long Draw Stud), or LS50 Battery-Powered Driver (LS50L11A)
- Material : Carbon Steel, Nickel Plated
- Minimum Pilot Hole : Recommended size: 7/8" (22.2 MM)
- Operation : Must be used with other SPEEDPUNCH® System components
- Sub Brand : SPEED PUNCH®#174
- Type : Knockout Punches
- Weight : 0.80 lbs. (0.36 kg)