



PRODUCT SEARCH

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**TERMINALS**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

SITE-RITE® Hand Bender for 1/2" EMT

Cat #:

840

UPC #:

23533

Spec:

Capacity 1/2" - 1-1/4" EMT, 1/2" - 1" Rigid Weight 840 - 1.4 lbs. (.7 kg) 8840 - 3.1 lbs. (1.4 kg) 840H - 5.5 lbs. (2.5 kg) 8841 - 4.3 lbs. (2.0 kg) 841 - 2.1 lbs. (0.9 kg) 8842 - 7.2 lbs. (3.3 kg) 841H - 6.4 lbs. (2.9 kg) 8843 - 16.2 lbs. (7.3 kg) 842 - 3.5 lbs. (1.6 kg) 8840H - 7 lbs. (3.2 kg) 842H - 11 lbs. (5 kg) 8841H - 9 lbs. (4.1 kg) 843 - 8.3 lbs. (3.8 kg) 8842H - 15 lbs. (6.8 kg)

Description:

Handle straight up and down for 30 degree bends.

- Patented sight indicator on bender is a key feature for bending angles fast and easy.
- Non-slip, contoured pedal for added leverage.
- Strong, stable square hook design.
- Cast-in markings for stub-ups, saddle bends, back-to-back bends, and head-up or down bending.
-

© 2007 Greenlee Textron Inc., a subsidiary of [Textron Inc.](#) All rights reserved.
[Privacy Policy](#)
[Terms of Use](#)
[Careers](#)