



PRODUCT SEARCH

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)

TERMINATION

[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

100' x .175" (30.5 m x 4.4 mm) Fiberglass Fish Tape in Winder Case

Cat #:

540-100

UPC #:

35743

Spec:

Capacity 540 Series - .175" (4.4 mm) dia. - 400 lbs. (1.7 kN)
 maximum design strength 542 Series - 3/16" (4.7 mm) dia. - 300
 lbs. (1.3 kN) maximum design strength Weight 540-50 - 1.8 lbs. (0.8
 kg) 542-150 - 15 lbs. (6.8 kg) 540-100 - 2.1 lbs. (1 kg) 542-200 -
 16 lbs. (7.2 kg) R540-100 - 1.2 lbs. (0.6 kg) 542-250 - 17 lbs. (7.7
 kg)

Description:

12" (305 mm) case has high-impact nylon, one-piece handle for
 maximum

- durability, long life, and easy, comfortable use.
- Non-conductive fiberglass tape with low friction coating.
- Has unique non-coiling properties that enable it to fish in large and small conduit equally well, even with wire or cable in place.
- Exclusive, unique, lightweight reel for easy positive feed out and rewind.
- Excellent for installation of telecommunications and data communication cables in overhead plenums, above suspended ceilings and under floors.
- Fiberglass fish tape is the fastest manual fish tape available. It is
- intended for fishing only. Rope or line is recommended for pulling.



© 2007 Greenlee Textron Inc., a subsidiary of **Textron Inc.** All rights reserved.

[Privacy Policy](#) [Terms of Use](#) [Careers](#)