



PRODUCT SEARCH

[> SUPP](#)  
[> DIST](#)
[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**Navigation**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps &](#)[Miscellaneous](#)**Name:**

240 ft x 1/8 in x .060 in (61 m x 3.2 mm x 1.5 mm) Steel Fish Tape without Winder Case

**Cat #:**

R438-20

**UPC #:**

29048

**Spec:**

Capacity 1/8" (3.2 mm) and 1/4" (6.4 mm) tape width - 400 lbs. (1.7 kN) maximum design strength. Weight 438-10 - 5 lbs. (2.3 kg) R438-10 - 3 lbs. (1.4 kg) R538-10 - 6 lbs. (2.7 kg) 438-20 - 7 lbs. (3.2 kg) R438-20 - 6 lbs. (2.7 kg) R538-20 - 11 lbs. (5 kg) R438-5 - 2 lbs. (0.9 kg) 538-10 - 8 lbs. (3.6 kg)

**Description:**

- Tape made from oil tempered steel.
- High-impact nylon, one-piece handle for maximum durability, long life, and easy, comfortable use.
- Large handle grip for greater user control.
- Self-tensioning case for easy tape winding.
- Wide, impact-resistant rewinder case with viewports to ensure tape fit and retaining strap on inside to hold tape secure.

© 2007 Greenlee Textron Inc., a subsidiary of [Textron Inc.](#) All rights reserved.

[Privacy Policy](#) [Terms of Use](#) [Careers](#)