



PRODUCT DESCRIPTION

- Designed for a variety of entertainment ,display and gaming applications. Hyperline HDMI cables are a high-quality cable featuring multi-stranded copper conductors for highest possible signal strength and maximum frequency response. Also available in a 12A4P version which features corrosion-resistant gold connectors ensuring high conductivity for the best possible picture while supporting the highest resolution standards.

FEATURES

- 19 Pin Gold-plated connectors for highest signal transfer rate and resistance in corrosion
- Fully HDCP compliant to provide highest level of signal quality.
- Fully compliant to V1.4 and 2.0 specification.
- Supports Transfer Digital Audio and Video signals at warp speed of 10.2 Gigabits per second
- Full support 480i, 480p, 720p, 1080i, 1080p, 1044P resolution
- HDMI Ethernet Channel, Audio Return Channel
- 3D Support,4K x 2K Support

TECHNICAL SPECIFICATIONS

- Center Conductor Size: 30AWG , 26AWG
- Center Conductor Material: Bare Copper
- Insulation: Foam PE and Polypropylene
- Shielding Material: Aluminum Mylar
- Shielding Coverage: 100%Coverage plus 25%Overlap
- Connector Contact Plating: Gold Plated , 10Micro Inches Minimum
- Drain Wires: 30AWG Bare Copper
- Braiding: Aluminum
- Braiding Coverage: 70% Minimum
- Outside Material: Conductor Gauge Dependent
- Compliance: HDMI and ROHS



ORDERING

PC-HDMI-12A4P-XXFT-NB-BK	HDMI Patch Cord with Nylon Braid V1.4 (3,6,10,15,25 or 50FT)
PC-HDMI-12A4P-V2.0-XXFT-NB-BK	HDMI Patch Cord with Nylon Braid V2.0 (3,6,10,15,25 or 50FT)
PC-HDMI-12B1-XXFT-BK	HDMI Patch Cord Without Nylon Braid V1.4 (3,6,10,15,25 or 50FT)
PC-HDMI-12B1-V2.0-XXFT-BK	HDMI Patch Cord Without Nylon Braid V2.0 (3,6,10,15,25 or 50FT)
XX = 3, 6, 10, 15, 25, 35, 50 FT ZZZ = A4P, B1	



Toll Free: +1-866-634-9737

www.hyperline.com | info@hyperline.com



Toll Free: +1-888-497-3748