

OmniSeal™ Pro Compression Tools



- Factory pre-set to work with all IDEAL compression connectors and most major manufacturer's RG-59, RG-6, RG-6 Quad and RG-11 F-connectors
- Adjustable to fit multiple cables and other manufacturer's connectors
- High-strength aluminum body for durability and long life

Description	Cat. No.
OmniSeal™ Pro Compression Tool - F-type (RG-6, 59, 11), Mini F-type, RCA Mini Connectors	30-603
OmniSeal™ Pro XL Compression Tool - F-type (RG-6, 59, 11), Mini F-type, RCA Mini RCA and BNC Connectors	30-793

OmniSeal™ Compression Tools

- Lightweight and durable composite material
- High leverage design reduces hand fatigue



Feature	OmniSeal™ XL 30-703	OmniSeal™ 11 30-720
For RG-6 & RG-59 Cables	X	X
Compresses RCA & F-Connectors	X	X
Compresses BNC Connectors	X	—
Works with IDEAL and PPC brand RCA connectors	X	X
For RG-11 cables	—	X

Economy Compression Tool

- Easily compresses series 6 and 59 coax compression F-connectors
- Permanent connection - never comes loose
- Works with most brands of compression connectors
- Adjustable nesting fixture accommodates a variety of connectors



Description	Cat. No.
Economy Compression Tool	30-633
Economy Compression Tool Kit - Includes four 89-035 Connectors	33-653

CMP Compression Connectors

- Approved for use by most cable TV and satellite companies
- RF signal containment ensures strong signal
- Permanent connections do not pull off or come loose
- One-piece design for quick installation
- Compression port seal provides a water-tight seal for outdoor applications



Description	Qty.	Cat. No.
RG-59 Compression F-Connector	50	89-054
RG-59 Compression F-Connector	100	89-104
RG-6 Compression F-Connector	50	89-055
RG-6 Compression F-Connector	100	89-105
RG-6 Quad Compression F-Connector	50	89-056
RG-6 Quad Compression F-Connector	100	89-106

Universal Compression Connectors

- Four universal connectors terminate all plenum RG-6, RG-6, RG-59 and RG-11 braid types from 60% through quad shielding
- Approved by most satellite and cable TV companies
- Approved for indoor/outdoor use



Description	Qty.	Cat. No.
Universal RG-59 Compression Connectors	Jar of 50	89-059
	Jar of 100	89-159
Universal RG-6 Compression Connectors	Jar of 50	89-060
	Jar of 100	89-160
Plenum RG-6 Compression Connectors	Jar of 50	89-060P
	Jar of 100	89-160P
Universal RG-11 Compression Connectors	Clam of 10	89-011

BNC Compression Connectors

- Color coded by cable series for easy identification
- Approved for indoor/outdoor use



Description	Qty.	Cat. No.
BNC RG-6 Compression Connector	Clam of 15	89-057
BNC RG-6 Compression Connector	Jar of 50	89-5057
BNC RG-59 Compression Connector	Clam of 15	89-058
BNC RG-59 Compression Connector	Jar of 50	89-5058

Compression Tools/Connectors

Coaxial Selection Chart

Compression Style



Cable	Cutter	Stripper	Crimper	Connector	Tester
CATV/SATV/F-type					
RG-59	45-074, 45-075	45-265, 45-603, 45-320	30-603, 30-793, 30-703, 30-720, 30-633	89-054, 89-104, 89-059, 89-159	33-856, 33-880 33-881, 33-887*
RG-6	45-074, 45-075	45-262, 45-603, 45-320	30-603, 30-793, 30-703, 30-720, 30-633	89-055, 89-105, 89-060, 89-160	
RG-6 Quad Shield	45-074, 45-075	45-282, 45-603, 45-320	30-603, 30-793, 30-703, 30-720, 30-633	89-056, 89-106, 89-060, 89-160	
RG-6 & Quad 6 Plenum	45-074, 45-075	45-510	30-603, 30-793, 30-703, 30-720, 30-633	89-060P, 89-160P	
RG-11	45-074, 45-075	45-164, 45-510	30-603, 30-793, 30-720	89-011	
Minis	45-074, 45-075	45-529	30-603, 30-793, 30-703	89-014SM, 89-014SMRCA	
BNC					
RG-59	45-074, 45-075	45-265, 45-603, 45-320	30-603, 30-793, 30-703	89-058, 89-5058	
RG-6	45-074, 45-075	45-265, 45-603, 45-320	30-603, 30-793, 30-703	89-057, 89-5057	

Crimp Style



Cable	Cutter	Stripper	Crimper	Connector	Tester
CATV/SATV/F-Type					
RG-59	45-074, 45-075	45-265, 45-603, 45-320	30-503	85-036, 85-016, 86-016	33-856, 33-880 33-881, 33-887*
RG-6	45-074, 45-075	45-265, 45-603, 45-320	30-503	85-037, 85-017, 86-017	
RG-6 Quad Shield	45-074, 45-075	45-282, 45-603, 45-320	30-503	85-057, 85-030, 86-030	
RG-6 Plenum	45-074, 45-075	45-282, 45-603	30-503	N/A	
RG-11	45-074, 45-075	45-164, 45-510	N/A	N/A	
BNC					
RG-59, Non-Plenum	45-074, 45-075	45-520	30-502, 30-483	85-513, 85-517, 85-502	
RG-6 Non-Plenum	45-074, 45-075	45-520	30-483	85-545	

*Need LA-4173 adapter.