

Can-TWIST™ Wire Connectors

- Exceptional wire-range capacity, handles wire combinations from 22 to 8 AWG solid and/or stranded wires
- Spring threads are heat-set making them more reliable
- Flexible walls show when wires are firmly connected
- Extended skirt length provides over-strip protection
- Easily removed for repeat usage
- Smaller size makes it easier to work in tight spaces
- Wide mouth and square springs deliver quick pick-up
- Swept wings provide added gripping power
- Easier to twist. Only a few turns are necessary to achieve torque
- CSA 22.2 #188 Certified



Can-Twist
105°C/221°F



Can-Twist Extrême
High-Temp
150°C/302°F

CANADA'S BEST SELLING CONNECTOR

MODEL	COLOUR	WIRE COMBINATION RANGE	WIRE COMBINATION (MM)	QUANTITY	CAT. NO.
Can-Twist 007	Blue	600V No. 22 thru 8 Awg Min. 3 No. 22 Max 3 No. 10	600V .64mm DIA to 3.26mm DIA Min .97mm ² Max. 15.78mm ²	Pack of 15	30-157
				C-Pak of 100	30-207
				Jar of 175	30-107J
				Jar of 475	30-307J
				Bag of 500	30-607
				Jar of 1,000	30-707J
				Stubby of 7,500	30-817
				Barrel of 25,000	30-807
Can-Twist Extrême 007XT High-Temp	Black	600V No. 22 thru 8 Awg Min. 3 No. 22 Max 4 No. 11 (solid)	600V .64mm DIA to 3.26mm DIA Min .97mm ² Max. 13.24mm ²	Pack of 15	30-157XT
				Jar of 175	30-107XTJ
				Jar of 475	30-307XTJ
				Stubby of 7,500	30-817
				Barrel of 25,000	30-807XTJ

	3 # 22 1,920 (.97 mm ²)	3 # 14 12,330 (6.24 mm ²)	3 # 10 31,140 (15.78 mm ²)
Can-Twist 007	[Diagram showing wire combinations for Can-Twist 007]		
Combination CIR MIL Area	[Diagram showing CIR MIL area for Can-Twist 007]		
Can-Twist 007XT	3 # 22 1,920 (.97 mm ²)	3 # 14 12,330 (6.24 mm ²)	4 # 12 26,120 (13.44 mm ²)

Dimensions for Model Can-Twist 007/Can-Twist Extrême 007XT

DIMENSIONS	A	B	C	D	E
Inches	1/4	7/16	3/4	7/16	1 1/8
mm	7	11.5	19	11.5	29

Cu/Cu Only

Ask about volume pricing