



Project:	Type:	QTY:
Product Code:		

5"



## Product Code

**IP53 - SFL5SD - TRIM COLOR - INTENSITY - VOLTAGE**

W\*=White                      WW30\*=3000K                      120=120V, AC  
 A =Aluminum                      NW40 =4000K  
 CC =Custom Color

**Note: \* Components usually in-stock for quick assembly and shipping.**

## Features + Specifications

### Intended Use:

- Building interior
- Building exterior (ceiling recessed only)
- Damp location listed
- IC rated, approved and tested for direct contact with insulation materials

### Construction:

- Die-cast aluminum one piece trim frame with built-in heat sink
- Opal PMMA lens with light glide technology for even light distribution
- Full metal top plate protects LED PCB
- Heavy duty installation springs ensure tight fitting to ceiling

### Finish:

- W = Powder coat painted
- A = Anodized aluminum
- CC = Powder coat painted



### Optical System:

- High brightness 2835 SMDs with LM80 certificate **9W**
- **\*WW30 = 3000K CCT, 900 lumens** minimum with 80+ CRI
- Optional CCT color NW40 also available (This CCT might require minimum quantities with longer lead time)
- L70 @ 50000hrs for ambient temperature <25°C, 35000hrs >25°C
- PCB made from laminated heavy gauge copper materials

### Electrical System:

- Constant current driver technology
- 120V line voltage dimmable with most dimmers
- Overheat protected, RoHS compliant

Installation hole  
cut out size: 5-1/8" sq.



Right reserved for material and spec modification without prior notice.

Datecode 20151228

Warranty - Up To 3 Years

Certified to CSA C22.2 No.250.0 Conformed to UL 1598

Certification Marks (where applicable) will be found on our luminaires and its components



www.iplighting.com

