

T2.25-2
broches G4



T2.25-P13.5s



T2.5-BA9s



T3-E10



T3.25-BA9s



Les images ne sont pas à l'échelle. Toutes les lampes sont claires.

Code de commande	Description	Code de lampe	Forme	Culot	Tension (V)	Ampères (A)	Puissance (W)	Vie moyenne (h)	Diamètre (po) (mm)	HCL (po) (mm)	LHTM (po) (mm)	Qté paq.
13630	T2.25/CL/6V/1.33A/G4	785	T-2.25	2 broches G4	6.00	1.330	8	50	0.28 7.00	0.77 19.50	0.98 25.00	1
13633	T2.25/CL/6V/1.67A/G4	787	T-2.25	2 broches G4	6.00	1.670	10	100	0.28 7.00	0.77 19.50	0.98 25.00	1
13631	T2.25/CL/6V/2A/G4	786	T-2.25	2 broches G4	6.00	2.000	12	50	0.28 7.00	0.77 19.50	0.98 25.00	1
13622	8T2.25/CL/12V/G4	774	T-2.25	2 broches G4	12.00	0.667	8	50	0.24 6.00	0.77 19.50	0.75 19.00	1
13626	T2.25/CL/12V/1A/G4	783	T-2.25	2 broches G4	12.00	1.000	12	50	0.28 7.00	0.77 19.50	0.98 25.00	1
13845	T2.25/CL/2.8V/0.85A/P13.5S	HPR52	T-2.25	P13.5s	2.80	0.850	2	10	0.31 8.00	0.26 6.50	1.18 30.00	10
50242	T2.5/CL/24V/0.073A/BA9S/STD	24MB	T-2.5	BA9s	24.00	0.073	2	5000	0.31 7.80	0.79 20.00	1.18 30.00	10
10088	T2.5/CL/28V/0.04A/BA9S/STD	28MB	T-2.5	BA9s	28.00	0.040	1	5000	0.31 7.80	0.79 20.00	1.18 30.00	10
50517	T2.5/CL/60V/0.05A/BA9s/STD	60MB	T-2.5	BA9s	60.00	0.050	3	5000	0.31 7.80	0.79 20.00	1.18 30.00	10
50230	T2.5/CL/120V/0.025A/BA9s/STD	120MB	T-2.5	BA9s	120.00	0.025	3	5000	0.31 7.80	0.79 20.00	1.18 30.00	10
13423	4T3/CL/60V/E10	S.O.	T-3	E10	60.00	0.067	4	3000	0.36 9.15	0.98 25.00	1.18 30.00	10
50457	2T3.25/CL/6V/BA9s/STD	3895	T-3.25	BA9s	6.00	0.333	2	3000	0.41 10.30	0.55 14.00	0.98 25.00	10
50346	T3.25/CL/6.3V/0.15A/3M/BA9s/STD	47	T-3.25	BA9s	6.30	0.150	1	3000	0.41 10.30	0.78 19.80	1.18 30.00	10
50395	T3.25/6.3V/0.15A/20M/BA9S/STD	755	T-3.25	BA9s	6.30	0.150	1	20000	0.41 10.30	0.78 19.80	1.18 30.00	10
50344	T3.25/6.3V/0.25A/3M/BA9S/STD	44	T-3.25	BA9s	6.30	0.250	2	3000	0.41 10.30	0.78 19.80	1.18 30.00	10
50447	T3.25/6.3V/0.25A/5M/BA9s/STD	1866	T-3.25	BA9s	6.30	0.250	2	5000	0.41 10.30	0.78 19.80	1.18 30.00	10
50455	2T3.25/CL/12V/BA9s/STD	3796	T-3.25	BA9s	12.00	0.167	2	3000	0.41 10.30	0.55 14.00	0.98 25.00	10
50396	T3.25/CL/14V/0.08A/BA9S/STD	756	T-3.25	BA9s	14.00	0.080	1	15000	0.41 10.30	0.63 15.90	1.18 30.00	10
50432	T3.25/CL/14V/0.2A/BA9s/STD	1815	T-3.25	BA9s	14.00	0.200	3	3000	0.41 10.30	0.75 19.00	1.18 30.00	10
22074	T3.25/CL/14V/0.24A/BA9s/STD	1891	T-3.25	BA9s	14.00	0.240	3	500	0.41 10.30	0.63 15.90	1.18 30.00	10
50493	T3.25/CL/24V/0.06A/BA9s/STD	1437	T-3.25	BA9s	24.00	0.060	1	20	0.41 10.30	0.63 15.90	1.18 30.00	10
50456	2T3.25/24V/BA9s/STD	3797	T-3.25	BA9s	24.00	0.083	2	3000	0.41 10.30	0.55 14.00	0.98 25.00	10
50434	T3.25/CL/24V/0.17A/BA9s/STD	1818	T-3.25	BA9s	24.00	0.170	4	250	0.41 10.30	0.63 15.90	1.18 30.00	10
50240	T3.25/CL/28V/0.022A/BA9S/STD	1843	T-3.25	BA9s	28.00	0.022	1	3000	0.41 10.30	0.63 15.90	1.18 30.00	10
50435	T3.25/CL/28V/0.04A/BA9s/STD	1819	T-3.25	BA9s	28.00	0.040	1	1000	0.41 10.30	0.63 15.90	1.18 30.00	10
50442	T3.25/CL/28V/0.07A/BA9s/STD	1829	T-3.25	BA9s	28.00	0.070	2	1000	0.41 10.30	0.63 15.90	1.18 30.00	10
50397	T3.25/CL/28V/0.08A/BA9S/STD	757	T-3.25	BA9s	28.00	0.080	2	7500	0.41 10.30	0.63 15.90	1.18 30.00	10
50436	T3.25/CL/28V/0.1A/BA9s/STD	1820	T-3.25	BA9s	28.00	0.100	3	1000	0.41 10.30	0.63 15.90	1.18 30.00	10
50533	MIN T-3.25 28V 0.1A BA9s/BINGO	1820/B	T-3.25	BA9s	28.00	0.100	3	1000	0.36 9.18	0.98 24.78	1.09 27.72	10
50446	T3.25/28V/0.17A/1.5M/BA9s/STD	1864	T-3.25	BA9s	28.00	0.170	5	1500	0.41 10.30	0.63 15.90	1.18 30.00	10
50380	T3.25/CL/28V/0.17A/BA9S/STD	313	T-3.25	BA9s	28.00	0.170	5	500	0.41 10.30	0.63 15.90	1.18 30.00	10
50448	T3.25/CL/28V/0.2A/BA9s/STD	1873	T-3.25	BA9s	28.00	0.200	6	7000	0.41 10.30	0.63 15.90	1.18 30.00	10
50325	2T3.25/CL/30V/BA9/STD	SP-125	T-3.25	BA9s	30.00	0.067	2	3000	0.41 10.30	0.63 15.90	1.18 30.00	10
50438	T3.25/CL/36V/0.1A/BA9s/STD	1822	T-3.25	BA9s	36.00	0.100	4	1000	0.41 10.30	0.63 15.90	1.18 30.00	10
50441	T3.25/CL/37.5V/0.05A/BA9s/STD	1828	T-3.25	BA9s	37.50	0.050	2	3000	0.41 10.30	0.63 15.90	1.18 30.00	10

Cette liste ne comporte qu'une portion de la sélection de lampes miniatures disponibles chez STANDARD. Visitez notre site web pour consulter la sélection complète à www.standardpro.com