



Pictures are not to scale. All lamps are clear except where otherwise identified. **** Frost

Order code	Description	Lamp code	Shape	Base	Volts (V)	Amps (A)	Watts (W)	Average life (hrs)	Diameter (in.) (mm)	LCL (in.) (mm)	MOL (in.) (mm)	Pack qty
R												
13073	20R12/FR/13V/ BA15S	1383	R-12	BA15s	13.00	1.538	20	300	1.55 39.26	N/A N/A	2.60 66.00	10
13076	20R12/F/28V/ BA15S ****	1385	R-12	BA15s	28.00	0.714	20	300	1.55 39.26	N/A N/A	2.60 66.00	10
13837	25RP11/CL/12V/ BA15D/STD	EMR-1125	RP-11	BA15d	12.00	2.083	25	75	1.42 36.10	1.30 33.00	2.24 57.00	10
S												
50305	6S6/CL/6V/BA15D/STD	N/A	S-6	BA15d	6.00	1.000	6	1500	0.78 19.81	1.00 25.40	1.89 48.00	10
50302	6S6/CL/24V/BA15D/STD	N/A	S-6	BA15d	24.00	0.250	6	1500	0.78 19.81	1.19 30.20	1.89 48.00	10
50304	6S6/CL/32V/BA15D/STD	N/A	S-6	BA15d	32.00	0.188	6	1500	0.78 19.81	1.19 30.20	1.89 48.00	10
50291	6S6/CL/125V/BA15d/STD	N/A	S-6	BA15d	125.00	0.048	6	3000	0.78 19.81	1.19 30.20	1.89 48.00	10
50285	10S6/CL/125V/BA15d/STD	N/A	S-6	BA15d	125.00	0.080	10	1500	0.78 19.81	1.19 30.20	1.89 48.00	10
50295	6S6/CL/130V/BA15d/STD	N/A	S-6	BA15d	130.00	0.046	6	3000	0.78 19.81	1.19 30.20	1.89 48.00	10
50297	6S6/CL/145V/BA15d/STD	N/A	S-6	BA15d	145.00	0.041	6	3000	0.78 19.81	1.19 30.20	1.89 48.00	10
51145	10S6/CL/230V/BA15d/STD	N/A	S-6	BA15d	230.00	0.043	10	1500	0.78 19.81	1.19 30.20	1.89 48.00	10
50292	6S6/CL/12V/E12/STD	N/A	S-6	E12	12.00	0.500	6	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50301	6S6/CL/24V/E12/STD	N/A	S-6	E12	24.00	0.250	6	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50303	6S6/CL/32V/E12/STD	N/A	S-6	E12	32.00	0.188	6	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50306	6S6/CL/75V/E12/STD	N/A	S-6	E12	75.00	0.080	6	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50287	3S6/CL/125V/E12/STD	N/A	S-6	E12	125.00	0.024	3	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50290	6S6/CL/125V/E12/STD	N/A	S-6	E12	125.00	0.048	6	3000	0.78 19.81	1.31 33.30	1.89 48.00	10
50284	10S6/CL/125V/E12/STD	N/A	S-6	E12	125.00	0.080	10	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
52119	15S6/CL/125V/E12/STD	N/A	S-6	E12	125.00	0.120	15	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50288	3S6/CL/130V/E12/STD	N/A	S-6	E12	130.00	0.023	3	3000	0.78 19.81	1.31 33.30	1.89 48.00	10
50294	6S6/CL/130V/E12/STD	N/A	S-6	E12	130.00	0.046	6	3000	0.78 19.81	1.31 33.30	1.89 48.00	10
50296	6S6/CL/145V/E12/STD	N/A	S-6	E12	145.00	0.041	6	3000	0.78 19.81	1.31 33.30	1.89 48.00	10
50299	6S6/CL/230V/E12/STD	N/A	S-6	E12	230.00	0.026	6	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50286	10S6/CL/230V/E12/STD	N/A	S-6	E12	230.00	0.043	10	1500	0.78 19.81	1.31 33.30	1.89 48.00	10
50534	6S6/CL/120V/E17/STD	N/A	S-6	E17	120.00	0.050	6	1500	0.78 19.81	1.46 37.00	1.81 46.00	10
50324	9S8/CL/6V/BA15D/STD	EMS-0509	S-8	BA15d	6.00	1.500	9	75	1.00 25.40	1.25 31.80	2.01 51.00	10
50323	9S8/CL/12V/BA15D/STD	EMS-1109	S-8	BA15d	12.00	0.750	9	75	1.00 25.40	1.25 31.80	2.01 51.00	10
50918	S8/CL/12.8V/1.04A/BA15d/STD	94	S-8	BA15d	12.80	1.040	13	700	1.00 25.40	1.13 28.60	2.01 51.00	10
50413	S8/CL/12.8V/1.44A/BA15d/STD	1142	S-8	BA15d	12.80	1.440	18	1000	1.00 25.40	1.25 31.80	2.01 51.00	10
50321	9S8/CL/24V/ BA15D/STD	EMS-2209	S-8	BA15d	24.00	0.375	9	75	1.00 25.40	1.25 31.80	2.01 51.00	10
50319	18S8/CL/24V/ BA15D/STD	EMS-2218	S-8	BA15d	24.00	0.750	18	75	1.00 25.40	1.25 31.80	2.01 51.00	10
50426	S8/CL/28V/0.93 0.34A/DCI/STD	1662	S-8	BAY15d	28.00	0.340	10	1000	1.00 25.40	1.25 31.80	2.01 51.00	10
13040	S8/CL/28V/0.71A/BA15D	1204	S-8	BA15d	28.00	0.710	20	400	1.00 25.40	1.25 31.80	2.01 51.00	10
22119	S8/CL/28V/1.02A/BA15D/STD	1638	S-8	BA15d	28.00	1.020	29	500	1.00 25.40	1.25 31.80	2.01 51.00	10
22073	S8/CL/32V/0.45A/BA15D/STD	1228	S-8	BA15d	32.00	0.450	14	150	1.00 25.40	1.13 28.60	2.01 51.00	10
50690	S8/CL/40V/0.38A/BA15d/STD	1229	S-8	BA15d	40.00	0.380	15	400	1.00 25.40	1.13 28.60	2.01 51.00	10

This list only shows a portion of the whole selection of miniature lamps available at STANDARD'S. For a complete product listing visit our e-catalog at www.standardpro.com.