



# Low Profile Wall LED

## PW15-NW-G1-8-BZ

Low Profile Wall, LED, 15W, 4000K, 70 CRI, 120-277V, Bronze - 110 lm/W

The Low Profile Wall Mount features a discreet design that will complement any building exterior. Three sizes are available in 15, 30 and 50W output to accommodate multiple mounting heights. Low Profile Wall delivers up to 110 lumens per watt for excellent energy savings over HID.

### Product data

General Information	
Colour Temperature	4000K
CRI	70
Photometric Distribution Type	Type II
Mounting	Wall

  

Operating and Electrical	
Luminaire Input Watts	15
Voltages	120/208/240/277 V

  

Mechanical and Housing	
Shape	Rectangular

  

Initial Performance (IEC Compliant)	
Luminaire Lumens	1656

  

Efficacy	110 lm/W
----------	----------

  

Product Data	
Order product name	PW15-NW-G1-8-BZ
Catalog Number	PW15-NW-G1-8-BZ
EAN/UPC - Product	783352024299
Order code	912401468308
Catalog Number Description	Low Profile Wall, LED, 15W, 4000K, 70 CRI, 120-277V, Bronze
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	912401468308
Net Weight (Piece)	1.460 kg