



# Low Profile Wall LED

## PW30-NW-G1-8-BZ

Low Profile Wall, LED, 30W, 4000K, 70 CRI, 120-277V, Bronze - 103 lm/W

The Low Profile Wall Mount features a discreet design that will complement any building exterior. Three sizes are available in 15, 30 and 50W output to accommodate multiple mounting heights. Low Profile Wall delivers up to 110 lumens per watt for excellent energy savings over HID.

### Product data

General Information	
Colour Temperature	4000K
CRI	70
Mounting	Wall

  

Operating and Electrical	
Luminaire Input Watts	30
Voltages	120/208/240/277 V

  

Mechanical and Housing	
Shape	Rectangular

  

Initial Performance (IEC Compliant)	
Luminaire Lumens	3090
Efficacy	103 lm/W

Product Data	
Order product name	PW30-NW-G1-8-BZ
Catalog Number	PW30-NW-G1-8-BZ
EAN/UPC - Product	783352024305
Order code	912401468309
Catalog Number Description	Low Profile Wall, LED, 30W, 4000K, 70 CRI, 120-277V, Bronze
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	912401468309
Net Weight (Piece)	1.760 kg