



# Low Profile Wall LED

## PW50-NW-G1-6-BZ

Low Profile Wall, LED, 50W, 4000K, 70 CRI, 347V, Bronze - 93 lm/W

The Low Profile Wall Mount features a discreet design that will complement any building exterior. Three sizes are available in 15, 30 and 50W output to accommodate multiple mounting heights. Low Profile Wall delivers up to 110 lumens per watt for excellent energy savings over HID.

### Product data

General Information	
Colour Temperature	4000K
CRI	70
Photometric Distribution Type	Type II
Mounting	Surface
Operating and Electrical	
Luminaire Input Watts	55
Voltages	347 V
Mechanical and Housing	
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	5121

Efficacy	93 lm/W
Product Data	
Order product name	PW50-NW-G1-6-BZ
Catalog Number	PW50-NW-G1-6-BZ
EAN/UPC - Product	783352024343
Order code	912401468313
Catalog Number Description	Low Profile Wall, LED, 50W, 4000K, 70 CRI, 347V, Bronze
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401468313
Net Weight (Piece)	3.200 kg