



KFS-6



KFCB



KFWB



K4040



4041

ORDERING INFORMATION

MH, PULSE START ORDERING INFORMATION*			
CATALOG NUMBER	LAMP AND WATTAGE	VOLTS ④	BEAM SPREAD H° X V°
KFP150-76 KFP155-76	150 MHP M-102/142	QUAD 480	7 (145°) X 6 (114°)
KFP170-76 KFP175-76	175 MH M-137/152	QUAD 480	7 (145°) x 6 (114°)
KFP200-76 KFP205-76	200 MH M-136	QUAD 480	7 (145°) x 6 (114°)
KFP250-76 KFP255-76	250 MHP M-138	QUAD 480	7 (145°) x 6 (114°)
KFP320-76 KFP325-76	320 MHP M-132	QUAD 480	7 (146°) x 6 (119°)
KFP350-76 KFP355-76	350 MHP M-131	QUAD 480	7 (146°) x 6 (119°)
KFP400-76 KFP405-76	400 MHP M-135	QUAD 480	7 (146°) x 6 (119°)

HPS, MH, START ORDERING INFORMATION*				
CATALOG NUMBER	LAMP AND WATTAGE	VOLTS ④	BEAM SPREAD H° X V°	
KFS070-76 KFS075-76	70 HPS M-102/142	QUAD 480	7 (144°) X 6 (113°)	
KFS100-76 KFS105-76	100 HPS M-137/152	QUAD 480	7 (145°) x 6 (114°)	
KFS150-76 KFS155-76	150 HPS S-55	QUAD 480	7 (144°) x 6 (113°)	
KFS250-76 KFS255-76	250 HPS S-50	QUAD 480	7 (144°) x 6 (113°)	
KFS400-76 KFS405-76	400 HPS S-51	QUAD 480	7 (144°) x 6 (113°)	
KFS1000-76 KFS1005-76	1000 HPS S-52 ④⑤	QUAD 480	7 (130°) x 6 (114°)	
EXPORT ONLY	KFH170-76 KFH175-76	170 MH M-57	QUAD 480	7 (145°) x 6 (114°)
	KFH250-76 KFH255-76	250 MH M-58	QUAD 480	7 (145°) x 6 (114°)
	KFH400-76 KFH405-76	400 MH M-59	QUAD 480	7 (146°) x 6 (119°)
	KFH1000-76 KFH1005-76	1000 MH M-47 ④⑥	QUAD 480	7 (145°) x 6 (114°)

* Consult T-Code Chart for hazardous location suitability.
 ④ Consult factory for other available voltages.
 ⑤ 1000 watt fixture aiming angle limited to 45°-135° (no straight up or down) 1000 watt fixtures are rated and listed for 40° ambient.
 ⑥ Use Philips C1000S52/ED37 11-1/2" lamp.

KF MOUNTING ACCESSORIES ①	
CATALOG NUMBER	DESCRIPTION
KFS-6	Steel slipfitter for 2" pipe (2-3/8" o.d.) tenon. Slips 3.75" over pipe.
KFCB	Heavy duty cast-iron crossarm fitting for horizontal trunnion
KFWB	Heavy duty wall mount and/or pipe clamp fitting Clamps 2" pipe (2-3/8" o.d.) thru 2-1/2" pipe (2-7/8" o.d.)
K4040	Heavy duty steel wall bracket. (Must use with KFCB crossarm fitting)
4041	Heavy duty steel wall bracket 2" pipe (2-3/8" o.d.) tenon fitting
KF-Door	Replacement Door & Lens assembly

① Fittings available to adapt trunnion mount floodlights to crossarms, poles and walls. Must be ordered separately.