



[View More +](#)



2105

### Penlight

★★★★★ 4.7 (12) [Write a review](#)

**BRIGHTER, CLEARER, EASIER INSPECTIONS.** The Milwaukee® Penlight delivers 100 lumens of TRUEVIEW™ High Definition output. Illuminate more area with brighter, natural light for the truest colors and details. A protective rubber bite zone lets users safely direct light while performing two handed tasks. Waterproof and dustproof, this penlight is sealed to withstand the toughest jobsite conditions. The Penlight's 6000 series aircraft aluminum body and lens are impact and corrosion resistant. Use the penlight's metal clip to attach to any chest or pant pocket for quick, everyday use. The Milwaukee® Penlight is covered by a limited lifetime warranty.

[Close](#)

#### INCLUDES:

(2) AAA Batteries

#### KEY FEATURES

#### SPECIFICATIONS

#### REVIEWS

✓ 100 Lumens of TRUEVIEW™ High Definition Output

✓ Protective Rubber Bite Zone

✓ On/Off and Momentary-On Button

✓ Impact and Chemical Resistant Lens

✓ 43 Meter Beam Distance

✓ IP67 Rated: Waterproof and Dustproof

✓ 6000 Series Aircraft Aluminum Body

✓ Removable Metal Clip

✓ Powered by (2) AAA Batteries (Included)

✓ Limited Lifetime Warranty (Excludes Batteries)