

## 14" Enclosure with Hinged Door

EN1450



This 14" enclosure features universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It also includes a hinged cover.

### features & benefits

- Flanged covers hide drywall openings
- Drywall depth indicators
- Flush and surface installation
- Mounting tabs provide correct flush-mount position for standard installations
- Patented mounting system offers versatile module mounting options
- Includes self-adhesive cable identification table
- Cover included
- Made in the USA

### specifications

#### General Info

Color: Glossy White  
finish: Protective Powder Coat  
Type: Hinged

#### Listing Agencies/Third Party Information

cULus: Yes  
UL Listing No: ANSI/UL 1863;ANSI/UL 985;ANSI/UL 1023; CAN/CSA-C22.2 No. 182.4-1990;ULC-S545;CSA-C22.2 No. 144.1 (2006) -- (Communication Circuit Accessory) and (Security Equipment - Fire Alarm Equipment)

#### Dimensions

Depth U S: 3.7"

Height U S: 14.1"

Width U S: 14.3"

Primary Package Weight U S: 9.5 lb

Product Weight U S: 8.5 lb

#### **Technical Information**

Humidity: Max 93% non-condensing

Material: 20 Gage CRS

Minimum Depth Requirement U S: 3.7"

Mounting: Surface or Flush