

## 28" Enclosure with Hinged Door

EN2850



This 28" enclosure is the perfect solution for a basic structured wiring system. It features larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It includes a hinged cover.

### features & benefits

- Flanged covers hide drywall openings
- Drywall depth indicators
- Flush and surface installation
- Mounting tabs provide correct flush-mount position for standard installations
- Patented mounting system offers versatile module mounting options
- Literature pouch included for dealer information
- Includes self-adhesive cable identification table
- Cover included
- Made in the USA

### specifications

#### General Info

Color: Glossy White  
finish: Protective Powder Coat  
Type: Hinged

#### Listing Agencies/Third Party Information

cULus: Yes  
UL Listing No: ANSI/UL 1863;ANSI/UL 985;ANSI/UL 1023; CAN/CSA-C22.2 No. 182.4-1990;ULC-S545;CSA-C22.2 No. 144.1 (2006) -- (Communication Circuit Accessory) and (Security Equipment - Fire Alarm Equipment)

#### Dimensions

Depth U S: 3.7"

Height U S: 28"

Width U S: 14.3"

Primary Package Weight U S: 16.0 lb

Product Weight U S: 15.0 lb

### **Technical Information**

Humidity: Max 93% non-condensing

Material: 20 Gage CRS

Minimum Depth Requirement U S: 3.7"

Mounting: Surface or Flush