

42" Enclosure with Screw-On Cover

EN4200



Perfect for larger installations, this 42" enclosure features universal On-Q style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It includes a screw-on cover.

Also available with Hinged & No Covers.

features & benefits

- Flanged covers hide drywall openings
- Drywall depth indicators
- Flush and surface installation
- Mounting tabs provide correct flush-mount position for standard installations
- Patented mounting system offers versatile module mounting options
- Literature pouch included for dealer information
- Includes self-adhesive cable identification table
- Cover included
- Made in the USA

specifications

General Info

Color: Glossy White
finish: Protective Powder Coat
Type: Screw-On

Listing Agencies/Third Party Information

cULus: Yes
UL Listing No: ANSI/UL 1863;ANSI/UL 985;ANSI/UL 1023; CAN/CSA-C22.2 No. 182.4-1990;ULC-S545;CSA-C22.2 No. 144.1 (2006) -- (Communication Circuit Accessory) and (Security Equipment - Fire Alarm Equipment)

Dimensions

Depth U S: 3.7"

Height U S: 42.1"

Width U S: 14.3"

Primary Package Weight U S: 23.51 lb

Product Weight U S: 21.51 lb

Technical Information

Humidity: Max 93% non-condensing

Material: 20 Gage CRS

Minimum Depth Requirement U S: 3.7"

Mounting: Surface or Flush