

24VDC 60W Power Supply

PW1060



Powers the lyriQ Audio Module, LCD Module, and Universal Power Distribution Module.

features & benefits

24 VDC, 60 W, 2.5 Amp Power Supply

specifications

General Info

Type: Power Supply
Housing Material: High Impact Flame Retardant Plastic

Listing Agencies/Third Party Information

cULus: Yes
FCC Standard: Yes
UN SPS C: 39121006

Dimensions

Height Metric: 3.5 cm
Height U S: 1.38"
Length U S: 4.72"
Length Metric: 12 cm
Width Metric: 6 cm
Width U S: 2.36 in

Cord Information

Cord Length Metric: 61 cm
Cord Length U S: 24"

Technical Information

AC Voltage Input: 100-240VAC
Amps: 2.5A
Efficiency: 0.78
Humidity: 10% to 90% Humidity
Mounting: Desktop
Operating Temperature Celsius: 0°C to 40°C
Operating Temperature Fahrenheit: 32°F to 104°F
Volts D C: 24 VDC
Watts: 60W
Receptacle Type: DC Barrel Jack
Number Of Receptacles: 1