

Pre-Configured 1-Port Strap, 1 RJ45, White

WP3210-WH



This pre-configured RJ45 strap provides a quick and easy one port installation into any decorator opening.

features & benefits

Fits into any decorator opening.
Contains one RJ45 connection.

specifications

General Info

Color: White
Pair Count: 4
Termination: 8P8C
Type: Preconfigured Decorator Strap
Input Plug Type: RJ45 Male

Listing Agencies/Third Party Information

UL Standard: Yes
UN SPS C: 39121704

Dimensions

Depth Metric: 3.3 cm
Depth U S: 1.29"
Height Metric: 10.6 cm
Height U S: 4.19"
Width Metric: 4.2 cm

Width U S: 1.65 in

Technical Information

Current Max: 1.5A at 20°C

Flammability Rating: UL94-V0

Humidity: Maximum 93% Noncondensing

Material: High Impact Flame Retardant Plastic

Mounting: Wall Box

Operating Temperature Celsius: -10°C to 60°C

Operating Temperature Fahrenheit: 14°F to 140°F

Storage Temperature: -40°C to 70°C

Receptacle Type: 1x RJ45

Number Of Receptacles: 1