
15A, 125V WATERTIGHT STRAIGHT BLADE PLUG, YELLOW

14W47 | [Pass & Seymour](#)



FEATURES & BENEFITS

Rated watertight for 1,500 psi high-pressure hosedown, P&S plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.

- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.
- Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.
- Devices resist high-pressure hose down of 1,500 psi.
- Color-coded sealing bushings provided for a large range of cord diameters.
- Large ribs on body for a superior grip when mating.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Yellow

Type: Plug

Features: Watertight

Number Of Poles: 2 Pole

Number Of Wires: 3 Wire

Special Features: Watertight

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42M

CSA Standard: Yes

Federal Spec: Yes

UL Listing No: E146159

UL Standard: Yes

UN SPSC: 39121402

DIMENSIONS

Diameter (US): 1.63"

Length (US): 2.68"

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15P

NEMA Rating: 4X/6P

Volts: 125V

Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

