

Spec Grade Dead Front 20A GFCI, White

2085W



From the innovator of the product category, comes a full range of Pass & Seymour GFCI receptacles to enhance safety, shorten installation times and increase productivity on the jobsite. With high-impact-resistant, thermoplastic construction, our spec-grade GFCI are the most durable GFCI available. Also features patented SafeLock™ Protection—if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected.

features & benefits

- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. FSUL Listed (Federal Specification WC596). Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire. Two back wire holes per terminal. GFCIs with Auto-Ground assure a positive ground to metal box.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- Extra-long strap. Button colors match the device face. Dual-direction test and reset buttons. Class A rated GFCI. Supplied with matching TP26 nylon wall plate. Tri-drive screws.
- 10kA short circuit rating.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: White
Available Colors: Black, Ivory, Light Almond,White
Type: Dead Front
Style: Decorator

Listing Agencies/Third Party Information

CSA Standard: C22.2 No. 42, 144
cULus: Yes
cUL Standard: Yes
UL Listing No: UL498
UL Listed: Yes
UL Standard: Yes
UN SPS C: 39121614

Dimensions

Depth U S: 0.98"
Height U S: 4.2"
Length U S: 4.20"
Width U S: 1.72"

Technical Information

Amps: 20A
NEMA Configuration Number: 5-20R
NEMA Rating: Yes
Volts: 125V
Volts A C: 125
Grade Type: Specification

Buy American Act Compliance

Country of Origin: CHINA
Buy American Act Status: No