

Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 15A, 250V, Ivory

5662I



Heavy-Duty Spec Grade Duplex Receptacle
Back & Side Wire 15amp 250volt Ivory



features & benefits

- Heavy-duty, brass strap for added strength and ground conductivity.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- High strength nylon face.
- Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.
- Eight back wire holes.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: Ivory
Type: Receptacles
Duty: Heavy Duty
Special Features: Back, Side Wire

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121406
UR: No

Dimensions

Depth U S: .780"
Height U S: 3.281"
Width U S: 1.322"

Technical Information

Amps: 15A
Volts: 250V
Volts A C: 250
Capacity: Duplex
Grade Type: Specification

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant