

# Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 250V, White

5862W



Heavy-Duty Spec Grade Duplex Receptacle  
Back & Side Wire 20amp 250volt White



## features & benefits

- Heavy-duty, brass strap for added strength and ground conductivity.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- High strength nylon face.
- Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.
- Eight back wire holes.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## specifications

### General Info

Color: White  
Type: Receptacles  
Duty: Heavy Duty  
Special Features: Back, Side Wire

### Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes  
Federal Spec: Yes  
Fed Spec Number: WC596  
UL Listing No: UL498  
UL Standard: Yes  
UN SPS C: 39121406  
UR: No

**Dimensions**

Depth U S: .780"  
Height U S: 3.281"  
Width U S: 1.322"

**Technical Information**

Amps: 20A  
Volts: 250V  
Volts A C: 250  
Capacity: Duplex  
Grade Type: Specification

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant