

Commercial Spec Grade Receptacle, Side Wire, 15A, 125V, Ivory

CR15I



Commercial Spec Grade Duplex Receptacle, Side Wire 15amp 125volt, Ivory



features & benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: Ivory
Type: Receptacles
Special Features: Side Wire

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42
CSA Standard: Yes
cURus: No

Federal Spec: No
UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121406
UR: No

Dimensions

Depth U S: 0.78"
Height U S: 3.281"
Width U S: 1.322"

Technical Information

Amps: 15A
Volts: 125V
Volts A C: 125
Capacity: Duplex
Grade Type: Commercial

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant