

# Commercial Spec Grade Receptacle, Side Wire, 20A, 125V, Ivory

CR20I



Commercial Spec Grade Duplex  
Receptacle, Side Wire 20amp 125volt, Ivory



## features & benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## specifications

### General Info

Color: Ivory  
Type: Receptacles  
Special Features: Side Wire

### Listing Agencies/Third Party Information

RoHS: Yes  
CSA Listing Info: C22.2 No. 42  
CSA Standard: Yes

Federal Spec: No  
UL Listing No: UL498  
UL Standard: Yes  
UN SPS C: 39121406

**Dimensions**

Depth U S: 0.78"  
Height U S: 3.281"  
Width U S: 1.322"

**Technical Information**

Amps: 20A  
NEMA Configuration Number: 5-20R  
Volts: 125V  
Volts A C: 125  
Capacity: Duplex  
Grade Type: Commercial

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant