

# Tamper-Resistant Floor Box Assembly - One Gang for Wood Sub-Floors

FB1TRDRN



Tamper-Resistant Floor Box Assembly. #8 duplex opening. Two threaded screw plug, Includes 3232 15 amp, 125 volt tamper-resistant receptacle. Nickel.

## features & benefits

- Tamper-Resistant shutters let plugs in, keep other things out.
- Rugged diecast cover plates.
- Meets UL514(c) and NEC 314.27(c).
- Scrub water compliant.
- With durable nickel or brass cover plates.
- Dual-voltage models available.
- Swing brackets mounting option eliminates drilling tile flooring for mounting screws.
- Wood sub-floors only.
- Wire Fill (AWG): 10 No. 14, 9 No. 12, 8 No. 10.



## specifications

### General Info

Product Series: Slater  
Component Type: Full Assemblies

### Listing Agencies/Third Party Information

CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPS C: 39121308  
UR: No

**Dimensions**

Depth U S: 4  
Length U S: 4.75  
Width U S: 3.25  
Volume: 20.5

**Technical Information**

Material: Nickel  
Floor Type: Wood

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant