

# MaxGrip M3 Plug, Yellow

PS5666Y



Straight Blade Plug 2pole 3wire 15amp  
250v

## features & benefits



- Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements; arc resistance exceeds UL requirements.
- Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws; close hinge housing around cord and tighten housing screws.
- Enclosed terminals provide solid, internally-clamped connections.
- Molded finger grips promote safe, sure handling.
- High-visibility yellow and orange, or gray.
- Hospital Grade version displays the Hospital Grade green dot.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## specifications

### General Info

Color: Yellow

### Listing Agencies/Third Party Information

cULus: Yes  
cURus: No  
Federal Spec: Yes  
Fed Spec Number: WC596  
UN SPS C: 39121402  
UR: No

**Dimensions**

Height U S: 1.83"

Width U S: 1.34"

**Technical Information**

Volts A C: 250

**Buy American Act Compliance**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant