

MaxGrip M3 Plug, Yellow

PS5965Y



Straight Blade Plug 2pole 3wire 15amp
125v

features & benefits



- Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements; arc resistance exceeds UL requirements.
- Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws; close hinge housing around cord and tighten housing screws.
- Enclosed terminals provide solid, internally-clamped connections.
- Molded finger grips promote safe, sure handling.
- High-visibility yellow and orange, or gray.
- Hospital Grade version displays the Hospital Grade green dot.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: Yellow
Product Series: MaxGrip
Type: Plug

Listing Agencies/Third Party Information

RoHS: Yes
CSA Listing Info: Yes
cULus: Yes
cURus: No

Federal Spec: No
UL Listing No: Yes
UN SPS C: 39121402
UR: No

Dimensions

Height U S: 1.83"
Width U S: 1.34"

Technical Information

Amps: 15A
Volts: 125V
Volts A C: 125

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant