



## BLANK PLATES -- STRAP MOUNTED, TWO GANG, 430 STAINLESS STEEL

SL24 | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Smooth Metal Wall Plate, 2gang Blank, Strap Mounted, 430 Stainless Steel

- Type 430 Stainless Steel, magnetic: .032" nominal thickness.
- Brushed finish.
- Less corrosion-resistant than Type 302, but ideal for general service in high abuse applications in industrial plants, commercial, and industrial buildings.
- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

---

### SPECIFICATIONS

#### GENERAL INFO

Size: Standard  
Type: Strap Mount  
Style: Blank Plate

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPSC: 39121704  
UR: No

#### TECHNICAL INFORMATION

Material: 430 Stainless Steel

Mounting: strap mount

Capacity: 2-gang

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

