

Tamper-Resistant Commercial Grade Receptacles, Ivory, TR20I

TR20I



Tamper-Resistant Commercial Grade Receptacle, 20A, 125V, Ivory



features & benefits

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- High Impact resistant nylon face.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive steel terminal screws. Side wire only.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: Ivory
Type: Receptacles
Features: Tamper-Resistant
Number Of Poles: 2
Number Of Wires: 3
Special Features: Side Wire Only,Tamper-Resistant
Style: Duplex

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42
CSA Standard: Yes
cULus: Yes
UL Listing No: UL498
UL Standard: Yes

UN SPS C: 39121406

Dimensions

Depth U S: .65"
Height U S: 3.28"
Width U S: 1.32"

Technical Information

Amps: 20A
NEMA Configuration Number: 5-20R
Volts: 125V
Volts A C: 125
Capacity: Duplex
Grade Type: Commercial

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant