

Weatherproof Cover for Flanged Inlet/Outlet

WPG1



Industrial Grade Weatherproof Lift Cover For Flanged Inlet/Outlet, 1.96" Diameter Opening to Accommodate 15/20A Straight Blade, 15A Turnlok, 20403 Power Interrupter, Gray



features & benefits

- Unbreakable glass-filled polycarbonate construction to withstand years of job site abuse and harsh environmental exposure.
- Stainless steel mounting screws also resist corrosion.
- Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).
- Molded-in label area (2.8 sq. in.) for pre-printed or handwritten labels for identification of circuits, ratings and other application data.
- WPG1 and WPG2 have lockable bullnose for OSHA locktag/tagout compliance.
- Covers fit all competitive inlets and outlets.
- Pre-attached gaskets for easy installation and tight seal to panel or weatherproof box -- with no misaligned or collapsed gaskets.
- Tamper-proof hinge features permanent, locked-in pins for added security.

specifications

General Info

Color: Gray
Type: Covers
Duty: Heavy Duty
Special Features: Weatherproof

Listing Agencies/Third Party Information

CSA Listing Info: Yes

CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPS C: 39121305
UR: No

Dimensions

Height U S: 4.57"
Width U S: 2.85

Technical Information

Amps: 15A/20A
Material: Plastic

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant