



Hardwire Smoke Alarm with Hush®

Hush® feature ideal to silence nuisance alarm without removing the battery.

Features:



• **Ionization Technology** – Better at detecting fast flaming fires.



• **120V AC Direct-Wire** – Interconnects with up to 24 units, of which 18 can be initiating.



• **9V Battery Backup (included)** – Continuous protection in case of power failure.



• **Test Button** – Tests circuitry and verifies alarm operation.



• **Hush® Button** – Quickly silences nuisance alarms.

• **Low Battery Indicator** – Warning chirp sounds when battery needs replacement.

• **Interconnectable** – ANY unit that senses a problem automatically triggers ALL units throughout the home immediately, allowing extra time for escape.

Specifications:

Product dimensions:	6" x 6" x 1.5" deep
Colour / Case Pack	White / 6 units
Electrical Rating:	120V AC, 60Hz, 60mA, 9V Battery Backup
Wiring:	Quick connect plug with 8" pigtails
Audio Alarm:	85dB
Temperature Range:	40°F (4.4°C) to 100°F (37.8°C)
Humidity Range:	Up to 85% relative humidity
Sensor:	Ionization
Limited Warranty:	5 Year
Weight:	0.40lb
UPC:	0-47871-40381-3



P1275CA

