



FURNITURE POWER 2-OUTLET WITH USB-A UNIT- BLACK

RDZBK | [radiant](#)

FEATURES & BENEFITS

radiant Furniture Power Centers bring a sleek, modern design with the functionality of USB and traditional power together. Quick and easy installation means nearly every piece of furniture can be powered up and ready to recharge devices. A sleek design and tamper-resistant receptacles bring your furniture a step above ordinary.

- Simply cut an opening, insert, tighten clamps, snap on the bezel and plug in.
- A compact, low profile design mounts quickly into many surfaces using screw clamps instead of wood screws.
- Safe for spills and ready to mount in horizontal surfaces like table tops
- Two USB charging ports (5V, 3.1A total) to charge mobile devices as quickly as possible.
- Two tamper-resistant receptacles to protect yourself and your devices from damage or risk of injury.
- Available in three attractive shades to complement the style of your furniture: black, white, and nickel. Included bezel prevents exposed screws from being seen.
- The pass-thru plug allows you to plug another device such as a lamp into the back of the furniture power unit plug, ensuring you don't lose an outlet.
- Complies with part 15 of the FCC Rules and is ETL Listed to both US and Canadian safety standards.
- Version 2 models feature an optional push button switch that controls a cord-connected lighting fixture.
- Version available with [10' cord](#).

SPECIFICATIONS

GENERAL INFO

UL Standards Tested: cETLus Listed to UL962A, the Standard for Furniture Power Distribution Units and CSA C22.2 No. 21, the standard for Cord Sets and Power Supply Cords

DIMENSIONS

Depth (US): 2"

Height (US): 2 1/2"

Width (US): 5 5/8"

Overall Dimensions (US): 5 5/8" wide by 2 1/2" tall by 2 1/8" deep

TECHNICAL INFORMATION

Mounting: Mounts in vertical or horizontal position Any material up to 3/4" (19mm) thick

Operating Temperature (Celsius): 0°C to 65°C
Storage Temperature: -35°C to 85°C

COUNTRY OF ORIGIN

Country Of Origin: CHINA