



GE Push Buttons

C-2000™ Push Buttons

600 Volts Max. AC/300 Volts Max. DC
10 Amps. Continuous AC/2.5 Amps. Continuous DC

Power Supplies & Contact Blocks

Power Supplies

Type	Power Supply	Voltage	Incandescent		LED		Neon ^①		
			Catalog Number	List Price, GO-10GC	Catalog Number	List Price, GO-10GC	Catalog Number	List Price, GO-10GC	
Full Voltage, AC/DC	Screw Terminal	No lamp	P9PDNVO	\$17.50	—	—	—	—	
		6	P9PDNVA	21.00	P9PDNVAL*	\$36.00	—	—	
		12	P9PDNVB	21.00	P9PDNVBL*	36.00	—	—	
		24	P9PDNVD	21.00	P9PDNVDL*	36.00	—	—	
		48	P9PDNVG	21.00	P9PDNVGL*	36.00	—	—	
		60	P9PDNVH	21.00	—	—	—	—	
		110	—	—	—	—	P9DNVIN	\$25.00	
		120 (ac only)	—	—	—	P9PDNVJL*	36.00	—	
		130	P9PDNVL	21.00	—	—	—	—	
	220	—	—	—	—	P9PDNVMN	25.00		
	Screw Terminal, Flashing	24	P9PDMVD	51.00	P9PDMVDL*	66.00	—	—	
		120 (ac)	P9PDMVJ	51.00	P9PDMVJL*	66.00	—	—	
		Screw Terminal, Panel Test	No Lamp	P9PDTVO	32.50	—	—	—	—
			6	P9PDTVA	36.00	P9PDTVAL*	51.00	—	—
			12	P9PDTVB	36.00	P9PDTVBL*	51.00	—	—
			24	P9PDTVD	36.00	P9PDTVDL*	51.00	—	—
			48	P9PDTVG	36.00	P9PDTVGL*	51.00	—	—
			60	P9PDTVH	36.00	—	—	—	—
			110	—	—	—	—	P9PDTVIN	40.00
	120 (ac only)		—	—	—	P9PDTVJL*	43.50	—	
	130		P9PDTVL	36.00	—	—	—	—	
	220	—	—	—	—	P9PDTVMN	40.00		
	Quick-Connect Terminal	No lamp	P9PDNFO	17.50	—	—	—	—	
		6	P9PDNFA	21.00	P9PDNFAL*	36.00	—	—	
		12	P9PDNFB	21.00	P9PDNFBL*	36.00	—	—	
		24	P9PDNFD	21.00	P9PDNFDL*	36.00	—	—	
		48	P9PDNFG	21.00	P9PDNFGL*	36.00	—	—	
		60	P9PDNFH	21.00	—	—	—	—	
		110	—	—	—	—	P9DNFIN	25.00	
		120 (ac only)	—	—	—	P9PDNFJL*	36.00	—	
		130	P9PDNFL	21.00	—	—	—	—	
	220	—	—	—	—	P9PDNFMN	25.00		
	Transformer, 50/60 Hz, AC	Screw Terminal	48	P9PTNVG	42.50	P9PTNVGL*	57.50	—	—
			60	P9PTNVH	42.50	P9PTNVHL*	57.50	—	—
			110-120	P9PTNVJ	42.50	P9PTNVJL*	57.50	—	—
			220-250	P9PTNVN	42.50	P9PTNVNL*	57.50	—	—
277-280			P9PTNVR	42.50	P9PTNVRL*	57.50	—	—	
380			P9PTNVU	42.50	P9PTNVUL*	57.50	—	—	
415-440			P9PTNVW	42.50	P9PTNVWL*	57.50	—	—	
480-500			P9PTNVY	42.50	P9PTNVYL*	57.50	—	—	
550-600			P9PTNVZ	42.50	P9PTNVZL*	57.50	—	—	
Screw Terminal, Flashing			48	P9PTMVG	72.50	P9PTMVG L*	87.50	—	—
			60	P9PTMVH	72.50	P9PTMVHL*	87.50	—	—
			110-120	P9PTMVJ	72.50	P9PTMVJL*	87.50	—	—
		220-250	P9PTMVN	72.50	P9PTMVNL*	87.50	—	—	
		277-280	P9PTMVR	72.50	P9PTMVR L*	87.50	—	—	
		380	P9PTMVU	72.50	P9PTMVUL*	87.50	—	—	
		415-440	P9PTMWW	72.50	P9PTMWWL*	87.50	—	—	
		480-500	P9PTMYY	72.50	P9PTMYYL*	87.50	—	—	
		550-600	P9PTMVZ	72.50	P9PTMVZL*	87.50	—	—	
		Resistor, AC/DC	Screw Terminal, Standard	110-120	P9PRNVJ	35.00	—	—	—
				220-240	P9PRNVN	35.00	—	—	—
			Screw Terminal, Diode (ac only)	220-240	P9PRDVN	35.00	—	—	—
110-120				P9PRLVJ	35.00	—	—	—	
Screw Terminal, Long Life		110-120	P9PRLVJ	35.00	—	—	—		
		220-240	P9PRTVN	50.00	—	—	—		
Screw Terminal, Panel Test	220-240	P9PRTVN	50.00	—	—	—			
	220-240	P9PRTVN	50.00	—	—	—			
Low-Level Energy (Reed) ^② Full-Voltage	Quick-Connect Terminal	No Lamp	P9PDHF	17.50	—	—	—		

① Neon bulbs are recommended for use only with clear, red, and yellow lenses.

② For use with Reed Logic flange only.

* LED Colors

LED Color	Red	Green	Yellow	Orange	Blue	White
* Color Code	R	V	G	A	L	B

See Next Page ↗

9 PUSH BUTTONS