C S S E R I E S



TECHNOLOGY · PERFORMANCE · DESIGN

Renowned Infinity performance from affordable in-wall loudspeakers.



CS IN-WALL LOUDSPEAKERS.

The CS Series in-wall loudspeakers continue Infinity's longstanding commitment to accurate sound reproduction, delivering uncompromised performance in any stereo, multichannel home theater or whole-house music system.

EASY TO INSTALL.

The CS models feature mounting clamps that swing out to securely grip your wall from the inside. Because they need not be



mounted to a stud, the CS speakers can be placed for optimal sonic performance and installation ease.



ROUGH-IN FRAMES.

Optional rough-in frames are available for use in new-construction installations before drywall is installed.



SPECIFICATIONS: Frequency Range

Recommended

Amplifier Power Range
Sensitivity
(2.83V @ 1 meter)
Nominal Impedance
Crossover Frequency
Low-Frequency
Driver
High-Frequency
Driver(s)
External Dimensions
(W x H)
Mounting Cutout Size
(W x H)
Mounting Depth
Weight
Optional Preconstruction
Rough-In Frame











CS 50	CS 60	CS GOR	CS GORDT	CS 80R
48Hz — 20kHz (±3dB) 45Hz (—10dB)	45Hz — 20kHz (±3dB) 38Hz (—10dB)	50Hz — 20kHz (±3dB) 40Hz (—10dB)	50Hz — 20kHz (±3dB) 40Hz (—10dB)	45Hz — 20kHz (±3dB 32Hz (—10dB)
10 — 75 watts	10 — 100 watts	10 — 100 watts	10 — 100 watts total (50WPC)	10 — 100 watts
87dB	88dB	88db	88dB, both channels driven	89dB
8Ω	8Ω	8Ω	8Ω per input	8Ω
2,400Hz; 12dB/Octave	2,800Hz; 12dB/Octave	2,600Hz; 12dB/Octave	2,600Hz; 12dB/Octave	2,400Hz; 12dB/Octave
5-1/4" (130mm)	6-1/2" (165mm)	6-1/2" (165mm)	6-1/2" (165mm)	8" (200mm)
1" (25mm) with acoustical waveguide	1" (25mm) with acoustical waveguide	1" (25mm)	Dual 3/4" (19mm)	1" (25mm)
7-1/2" x 10" (191mm x 254mm)	8-1/2" x 11" (216mm x 279mm)	9-3/16" (Dia.) (233mm)	9-3/16" (Dia.) (233mm)	10-7/8" (Dia.) (275mm)
6-1/8" x 8-11/16" (156mm x 221mm)	7-1/8" x 9-11/16" (181mm x 246mm)	7-7/8" (Dia.) (200mm)	7-7/8" (Dia.) (200mm)	9-1/2" (Dia.) (240mm)
3-3/4" (95mm)	3-7/8" (98mm)	4-1/4" (108mm)	4-1/4" (108mm)	4-1/4" (108mm)
3 lb (1.4kg)	5 lb (2.3kg)	4.5 lb (2.0kg)	4 lb (1.8kg)	5.6 lb (2.5kg)
CS 50RIF	IW6 RIF	IW6R RIF	IW6R RIF	IW8R RIF



TECHNOLOGY · PERFORMANCE · DESIGN

250 Crossways Park Drive, Woodbury, NY 11797 USA 516.674.4INF (4463) Fax 516.682.3523 www.infinitysystems.com

H A Harman International Company © 2004 Harman International Industries, Incorporated Printed 8/04 Part No. CSSERIESPPI8/04
 Designed, edited and digitally produced by Harman Consumer Group Marketing & Design Center, Woodbury, NY.
 Infinity is a registered trademark of Harman International Industries, Incorporated.

Infinity continually strives to update and improve existing products, as well as create new ones. The specifications and construction details herein are therefore subject to change without notice.