

Features/Benefits

- ALTO® Lamp Technology Passes EPA's TCLP test for non-hazardous waste.
- Utilizes amalgam technology to provide > 90% of rated lumens in ambient temperatures from 23F to 130F.
- Triple tube design available in 18, 26, 32, and 42W.
- Excellent Color Rendering 82 Color Rendering Index (CRI).
- Broad Range of Color Temperature Available in 2700, 3000, 3500 and 4100K.
- Dimmable PL-T 4-pin lamps may be used with electronic dimming ballasts.
- Long Life 12,000 hours.
- Energy Saving Designed for use with electronic ballasts for lower operating costs and flicker-free starting.

Applications

· Ideal for downlights and medium bay multi-lamp fixtures for general lighting.

Notes

- Rated average life under specified test conditions with lamps turned off and restarted no more frequently than once every 3 operating hours. Lamp life is appreciably longer if lamps are started less frequently. (202)
- Approximate Initial Lumens. The lamp lumen output is based upon lamp performance after 100 hours of operating life, when the output is measured during operation on a reference ballast under standard laboratory conditions. (203)
- Design Lumens are the approximate lamp lumen output at 40% of the lamp's Rated Average Life. This output is based upon measurements obtained during lamp operation on a reference ballast under standard laboratory conditions. (208)

Product data		
268730		
PL-T 42W/830/4P 1CT		
268730		
1 Lamp in a Folding Carton		
1		
12		
046677268732		
	268730 PL-T 42W/830/4P 1CT 268730 1 Lamp in a Folding Carton 1	





Product data		
Case Bar Code	50046677268737	
Successor Product number		
Base	GX24q-4	
Base Information	4P	
Execution	/4P [4 Pins]	
Packing Type	1CT [1 Lamp in a Folding Carton]	
Packing Configuration	12	
Avg. Hrs. Life	16000 hr	
Ordering Code	PL-T 42W/830/4P/ALTO	
Pack UPC	046677268732	
Case Bar Code	50046677268737	
Watts	42W	
Lamp Voltage	- V	
Dimmable	Yes	
Color Code	830 [CCT of 3000K]	
Color Rendering Index	82 Ra8	
Color Designation	Warm White	
Color Description	830 Warm White	
Color Temperature	3000 K	
Initial Lumens	- Lm	
Initial Lumens	3200 Lm	
Overall Length C	158.4 mm	
Diameter D	39.85 mm	
Diameter D1	39.65 mm	
Product Number	268730	






PL-T 42W






Base GX24q-4



PL-T/830



PL-T/830

