


V-2S110-TP						
Brand Name	MARK III					
Ballast Type	Magnetic					
Starting Method	Rapid Start					
Lamp Connection	Series					
Input Voltage	277					
Input Frequency	60 HZ					
Status	Active					

Electrical Specifications

Lamp Type	Num. of Lamps	Rated Lamp Watts	Min. Start Temp (°F/C)	Input Current (Amps)	Input Power (Watts)	Ballast Factor	MAX THD %	Power Factor	Lamp Current Crest Factor	B.E.F
* F72T12/HO	2	85	-20/-29	0.75	201	0.98	20	0.97	1.8	0.49
F96T12/HO	2	110	-20/-29	0.90	245	0.98	20	0.98	1.7	0.40
F96T12/HO/ES	2	95	60/16	0.79	210	0.93	25	0.96	1.8	0.44




Diag. 21

The wiring diagram that appears above is for the lamp type denoted by the asterisk (*)

andard L				in.	cm
	in.	cm.	Yellow/Blue		
Black	22				
White	22	Blue/White	Blue/White		
			Brown		
Blue	46				
Red	46		Orange		
			Orange/Black		
Yellow	70		Black/White		
Gray					
Violet			Red/White		

Enclosure



Enclosure Dimensions

OverAll (L)	Width (W)	Height (H)	Mounting (M)
11.75 "	3.1875 "	2.625 "	11.14062 "
11 3/4	3 3/16	2 5/8	11 9/64
29.8 cm	8.1 cm	6.7 cm	28.3 cm

Revised 07/01/1999



Data is based upon tests performed by Philips Lighting Electronics N.A. in a controlled environment and is representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice. All specifications are nominal unless otherwise noted.

PHILIPS LIGHTING ELECTRONICS N.A.

10275 WEST HIGGINS ROAD · ROSEMONT, IL 60018 Tel: 800-322-2086 · Fax: 888-423-1882 · www.philips.com/advance Customer Support/Technical Service: 800-372-3331 · OEM Support: 866-915-5886