

These robust LED pucks, featuring a frosted lens, deliver highly efficient punches of white light. Well suited for under-cabinet lighting and a variety of other applications.









Can be surface or recessed Heat sink and thermal protection Ideal for highlighting display cabinets DImmable

MODEL

4005FR	1.5W single puck, 3000°K, 90 Lumens surface mounted adapter included
K4005FR	3 X 1.5W puck kit, 3000°K, 90 Lumens, each, surface mounted adapters included, includes a plug-in driver
4005HP	2.6W single puck, 3000°K, 230 Lumens, surface mounted adapter sold separately

SPECIFICATIONS

- 12V DC LED driver required.
- Over 50,000 hours of service life.
- 12" (30 cm) input lead with quick connector.
- 24" (61 cm) interconnection harness included.
- Warm white light output.
- Excellent color rendering.
- Superior LED performance and lifespan.
- Smooth 360°-wide spread.
- Minimal heat emission.
- Brighter than most equivalent 20W halogen pucks.
- Steel/aluminum construction.
- Frosted glass lens.
- Dimmable with most low-voltage electronic dimmers when used with DALS dimming power supply.

INSTALLATION

- For recess or surface installation, in any direction.
- Ideal for accent lighting inside or under any cabinet, shelf or display.
- A variety of power supplies and installation accessories available.

FINISH

ВК	Black		
WH	White		
SN	Satin nickel		

POWER SUPPLIES — PLUG-IN

ETR-LED10WPI	12VDC/10W	class 2	2 LED driver
ETR-LED24WPI	12VDC/24W	class 2	2 LED driver


POWER SUPPLIES — HARD-WIRED

BT06DIMLED-IC 6W dimmable LED hardwire driver BT12DIMLED-IC 12W dimmable LED hardwire driver BT24DIMLED-IC 24W dimmable LED hardwire driver 36W dimmable LED hardwire driver BT36DIMLED **BT48DIMLED** 48W dimmable LED hardwire driver

ACCESSORIES

4000E-24 4000E-60 4000HRNS-24

24" (61 cm) extension cord 60" (152.4 cm) extension cord 24" (61 cm) interconnection harness 4005HP-SURF-BK Surface mounted adapter, black 4005HP-SURF-SN Surface mounted adapter, satin nickel 4005HP-SURF-WH Surface mounted adapter, white



ORDERING EXAMPLE

4005FR-WH Would order a 4005 single puck with a 1.5W LED array with 90 Lumens at 3000°K in a white finish.